# **Optical Brinell Hardness**

# **Testing Machine**

ITS-3000-O



## **SCREEN**

Optical Screen Assembly attached to machine.

## **WORKSTAGE SIZE**

It is customizable as per customer requirement, std 200mm flat table and 70mm vee table comes with machine.

## **MEASURING RANGE**

1mm- 6mm

## **FOCUSING**

Auto focused optical tube fixed in machine.

## **WORKPIECE HEIGHT**

380 mm

## MEASURING SYSTEM

Measure dia on optical screen and attached micrometer after that in user manual provided dia and hardness correlation chart for results.

## **Throat Depth**

200 mm

#### RESOLUTION

1

## **MOVEMENT**

Sample resting screw Movement manually.

Loading unloading by handle controlled by hydraulic power pack.

## **POWER SUPPLY**

3 Phase with good earthing

## LOAD

kgf 250 to 3000 in stages of 250 kgf.

## **OPTIONAL**

Fabricated foundation table,
Different ranges of master test blocks,
5mm and 10mm ball indenters,
Double screw machine for heavy samples,
Brinell image analysis system for
computerized reports.